

Multi-position kit DPNC-40

Part number: 174419

FESTO



Data sheet

Feature	Value
Size	40
Corrosion resistance class (CRC)	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Ambient temperature	-40 °C...150 °C
Product weight	408 g
Note on materials	RoHS-compliant
Mounting material	Steel
Threaded pin material	Steel Galvanized
Nut material	Steel Galvanized