

# Multi-pin plug distributor MPV-E/A08-M8

Part number: 177669



## Data sheet

Feature	Value
Type of mounting	With through-hole With H-rail Optionally:
Product weight	100 g
Electrical connection technology I/O	M8 3-pin
DC operating voltage range	10 V...30 V
Acceptable current load per slot	1 A
Current rating	4 A
Degree of protection	IP65 In mounted state as per IEC 60529
Ambient temperature	-20 °C...80 °C
LABS (PWIS) conformity	VDMA24364-B2-L
Housing material	PA6-reinforced
Socket material	Brass