

Plastic pipe
PQ-PA-12X1,5X3000
Part number: 177728

FESTO



Data sheet

Feature	Value
Outside diameter	12 mm
Inside diameter	9 mm
Temperature-dependent operating pressure	-0.95 bar...15 bar
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Temperature of medium	-25 °C...75 °C
Ambient temperature	-25 °C...75 °C
Product weight by length	0.051 kg/m
Color	Black
Material of pneumatic tubing	PA