

Clamping cartridge KP-20-1400

Part number: 178458

FESTO



Data sheet

Feature	Value
Mounting position	Any
Clamping type with active direction	Both sides Clamped by spring, released by compressed air
Structural design	Hinge-down panes
Variants	Piston rod at one end
Operating pressure	1 MPa 10 bar
Release pressure	0.3 MPa 3 bar
Round material to be clamped	20 mm
Operating medium	Compressed air as per ISO 8573-1:2010 [7:4:4]
Information on operating and pilot media	Operation with oil lubrication possible (required for further use)
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Ambient temperature	-10 °C...80 °C
Static holding force	1400 N
Product weight	170 g
Seals material	NBR TPE-U(PU)
Material of spring	Spring steel
Housing material	Aluminum Anodized
Clamping jaws material	Brass
Material of piston	POM