

Sensor bracket
DASI-Q11-50-A-SR
Part number: 1797071

FESTO



Data sheet

Feature	Value
Size	50
Design	for T-slot
for piston Ø	Ø50
Structural design	Sensor rail
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Ambient temperature	-10 °C...60 °C
Product weight	75 g
Type of mounting	Clamped in T slot With through-hole and screw With slot nuts
Note on materials	RoHS-compliant
Material of screws	Steel Galvanized