

Low consumption air gun

LSP-1/4-C

Part number: 184318

FESTO



Data sheet

Feature	Value
Exhaust air function	Metered blowing
Operating pressure	0 bar...10 bar
Standard nominal flow rate	120 l/min
LABS (PWIS) conformity	VDMA24364 zone III
Noise level	90 dB(A)
Ambient temperature	-10 °C...50 °C
Product weight	125 g
Pneumatic connection	Internal thread G1/4
Housing material	PA6-reinforced