

# Manual override HAB-3/8

Part number: 184587

**FESTO**



## Data sheet

Feature	Value
Nominal width	11 mm
Mounting position	Any
Valve function	Exhaust element
Operating pressure	0 bar...10 bar
Standard nominal flow rate exhaust air 6->5 bar	165 l/min
Explosion prevention and protection	Zone 1 (ATEX) Zone 2 (ATEX) Zone 21 (ATEX) Zone 22 (ATEX)
Operating medium	Compressed air as per ISO 8573-1:2010 [7:4:4]
Information on operating and pilot media	Operation with oil lubrication possible (required for further use)
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Temperature of medium	-20 °C...80 °C
Ambient temperature	-20 °C...80 °C
Max. tightening torque	35 Nm
Type of mounting	Screw-in
Pneumatic connection 1	G3/8
Pneumatic connection 2	G3/8
Note on materials	RoHS-compliant
Housing material	Wrought aluminum alloy, anodized