



Air preparation unit LFR-3/4-D-MAXI-KD-A

Part number: 185754

FESTO



Data sheet

Feature	Value
Size	Maxi
Series	D
Actuator lock	Rotary knob with detent
Mounting position	Vertical +/- 5°
Grade of filtration	40 µm
Condensate drain	Fully automatic
Structural design	Shut off valve Filter regulator with pressure gauge Safety start-up valve
Max. condensate volume	80 cm³
Bowl guard	Metal bowl guard
Pressure gauge	with pressure gauge
Operating pressure	0.3 MPa...1.2 MPa 3 bar...12 bar 43.5 psi...174 psi
Pressure regulation range MPa	0.25 MPa...1.2 MPa
Pressure regulation range	2.5 bar...12 bar
Pressure regulation range psi	36.25 psi...174 psi
Max. pressure hysteresis	0.02 MPa 0.2 bar 2.9 psi
Standard nominal flow rate	5000 l/min
Operating medium	Compressed air as per ISO 8573-1:2010 [:-:-] Inert gas
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Air quality class at the output	Compressed air as per ISO 8573-1:2010 [7:8:4] Inert gas
Temperature of medium	-10 °C...60 °C
Ambient temperature	-10 °C...60 °C
Product weight	3100 g
Type of mounting	Line installation With accessories Optionally:

Feature	Value
Pneumatic connection 1	G3/4
Pneumatic connection 2	G3/4
Housing material	Die-cast zinc
Material of bowl	PC