

**Cable socket**  
**ASI-SD-FK**  
Part number: 18785



**Data sheet**

Feature	Value
Type of mounting	With through-hole
Mounting position	Any
Product weight	6.8 g
Electrical connection	2-pin Socket, straight
DC operating voltage range	75 V
Operating voltage range AC	60 V
Current rating	3 A
Connection cross section	1.5 mm <sup>2</sup>
Degree of protection	IP65
Ambient temperature with flexible cable installation	-5 °C...50 °C
Storage temperature	-30 °C...85 °C
LABS (PWIS) conformity	VDMA24364-B2-L
Note on materials	RoHS-compliant
Housing material	PA
Material of pin contacts	Bronze