

**Cable socket**  
**ASI-SD-PG-M12**  
Part number: 18789

**FESTO**



**Data sheet**

Feature	Value
Type of mounting	With union nut
Mounting position	Any
Product weight	27.6 g
Electrical connection	4-pin Socket, straight Screw terminal
Operating voltage range AC	125 V
Current rating	3 A
Cable fitting	Pg9
Connection cross section	0.75 mm <sup>2</sup>
Degree of protection	IP65 IP67
Ambient temperature	-40 °C...85 °C
LABS (PWIS) conformity	VDMA24364-B2-L
Note on materials	RoHS-compliant
Housing material	PA
Housing colour	Black
Material of union nut	Nickel-plated
Material of pin contacts	Bronze