

Adapter connector MKA-PG29-M40

Part number: 1879673

FESTO



Data sheet

Feature	Value
Mounting position	Any
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Ambient temperature	-40 °C...200 °C
Type of mounting	With thread
Note on materials	RoHS-compliant
Material of pneumatic fitting	Brass Nickel-plated