

# Suction gripper ESG-10

Part number: 189171

FESTO



## Data sheet

Feature	Value
Suction cup diameter	10 mm
Mounting position	Vertical
Special features	Anti-static
Structural design	Vacuum connection at top Vacuum connection at side with height compensation with long height compensation
Classification of suction cup holder	Size 3
Suction cup shape	Round bellows, 1.5 convolutions Round bellows, 3.5 convolutions Round, flat
Operating medium	Atmospheric air based on ISO 8573-1:2010 [7:::-]
Corrosion resistance class (CRC)	1 - Low corrosion stress
Ambient temperature	-30 °C...200 °C
Vacuum connection	M14x1 G1/8 QS-6 PK-4
Note on materials	RoHS-compliant
Suction cup material	BR FPM NBR PUR VMQ (silicone)