

# Suction gripper ESG-20X60

Part number: 189190

FESTO



## Data sheet

Feature	Value
Vacuum cup size	20x60 mm
Mounting position	Vertical
Structural design	Vacuum connection at top Vacuum connection at side with height compensation with long height compensation
Classification of suction cup holder	Size 5
Suction cup shape	Oval, flat
Operating medium	Atmospheric air based on ISO 8573-1:2010 [7::-]
Corrosion resistance class (CRC)	1 - Low corrosion stress
Ambient temperature	-10 °C...70 °C
Vacuum connection	G1/8 G1/4
Note on materials	RoHS-compliant
Suction cup material	NBR