

Vacuum suction cup holder

ESH-HA-4-QS

Part number: 189199

FESTO



Data sheet

| Feature | Value |
|--------------------------------------|---|
| Nominal width | 5 mm |
| Volume | 0.719 cm ³ |
| Mounting position | Any |
| Structural design | Vacuum connection at top |
| Classification of suction cup holder | Size 4 |
| Operating medium | Atmospheric air based on ISO 8573-1:2010 [7:::-] |
| Corrosion resistance class (CRC) | 1 - Low corrosion stress |
| LABS (PWIS) conformity | VDMA24364-A1-L |
| Ambient temperature | 0 °C...60 °C |
| Product weight | 30 g |
| Type of mounting | With lock nut |
| Suction cup mounting | M6 |
| Vacuum connection | QS-6 |
| Note on materials | RoHS-compliant |
| Seals material | NBR |
| Retaining bracket material | Aluminum Brass, nickel-plated POM Tempered steel High-alloy steel |