

Vacuum suction cup holder

ESH-HB-3-PK

Part number: 189208

FESTO



Data sheet

Feature	Value
Nominal width	2.5 mm
Volume	0.313 cm ³
Mounting position	Any
Structural design	Vacuum connection at side
Classification of suction cup holder	Size 3
Operating medium	Atmospheric air based on ISO 8573-1:2010 [7:::-]
Corrosion resistance class (CRC)	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-A1-L
Ambient temperature	-10 °C...60 °C
Product weight	27 g
Type of mounting	With internal thread
Suction cup mounting	M4
Vacuum connection	PK-4
Note on materials	RoHS-compliant
Seals material	NBR Steel
Retaining bracket material	Aluminum Brass, nickel-plated POM Tempered steel High-alloy steel