

# Vacuum suction cup holder

## ESH-HB-5-G

Part number: 189211

FESTO



### Data sheet

Feature	Value
Nominal width	8.5 mm
Volume	1.921 cm <sup>3</sup>
Mounting position	Any
Structural design	Vacuum connection at side
Classification of suction cup holder	Size 5
Operating medium	Atmospheric air based on ISO 8573-1:2010 [7:::-]
Corrosion resistance class (CRC)	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-A1-L
Ambient temperature	-10 °C...60 °C
Product weight	91 g
Type of mounting	With internal thread
Suction cup mounting	M10
Vacuum connection	G1/8
Note on materials	RoHS-compliant
Retaining bracket material	Aluminum Brass, nickel-plated POM Tempered steel High-alloy steel