

Vacuum suction cup holder

ESH-HDL-1-QS

Part number: 189243

FESTO



Data sheet

Feature	Value
Suction cup holder height compensator	10 mm
Nominal width	3 mm
Volume	0.272 cm ³
Mounting position	Vertical
Structural design	Vacuum connection at side with height compensation
Classification of suction cup holder	Size 1
Operating medium	Atmospheric air based on ISO 8573-1:2010 [7:::-]
Corrosion resistance class (CRC)	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-A1-L
Ambient temperature	0 °C...60 °C
Product weight	29 g
Type of mounting	With lock nut
Suction cup mounting	Diameter 3 mm
Vacuum connection	QS-4
Note on materials	RoHS-compliant
Seals material	NBR Steel
Retaining bracket material	Aluminum Brass, nickel-plated POM Tempered steel High-alloy steel