

# Vacuum suction cup holder

## ESH-HDL-3-QS

Part number: 189247

FESTO



### Data sheet

| Feature                               | Value   |
|---------------------------------------|---|
| Suction cup holder height compensator | 20 mm   |
| Nominal width                         | 3.3 mm  |
| Volume                                | 0.474 cm <sup>3</sup>   |
| Mounting position                     | Vertical  |
| Structural design                     | Vacuum connection at side<br>with height compensation                         |
| Classification of suction cup holder  | Size 3  |
| Operating medium                      | Atmospheric air based on ISO 8573-1:2010 [7::-]                               |
| Corrosion resistance class (CRC)      | 1 - Low corrosion stress  |
| LABS (PWIS) conformity                | VDMA24364-A1-L  |
| Ambient temperature                   | 0 °C...60 °C  |
| Product weight                        | 65 g  |
| Type of mounting                      | With lock nut   |
| Suction cup mounting                  | M4  |
| Vacuum connection                     | QS-6  |
| Note on materials                     | RoHS-compliant  |
| Seals material                        | NBR<br>Steel  |
| Retaining bracket material            | Aluminum<br>Brass, nickel-plated<br>POM<br>Tempered steel<br>High-alloy steel |