

# Vacuum suction cup holder

## ESH-HE-1-M3

Part number: 189253

FESTO



### Data sheet

Feature	Value
Nominal width	1.2 mm
Volume	0.04 cm <sup>3</sup>
Mounting position	Any
Structural design	Vacuum connection at top
Classification of suction cup holder	Size 1
Operating medium	Atmospheric air based on ISO 8573-1:2010 [7:::-]
Corrosion resistance class (CRC)	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-A1-L
Ambient temperature	-10 °C...60 °C
Product weight	1 g
Type of mounting	With external thread Via vacuum connection
Suction cup mounting	Diameter 3 mm
Vacuum connection	M3
Note on materials	RoHS-compliant
Seals material	Wrought aluminum alloy NBR POM Steel
Retaining bracket material	Tempered steel