

Vacuum suction cup holder

ESH-HE-5-G1/4

Part number: 189257

FESTO



Data sheet

| Feature | Value |
|--------------------------------------|--|
| Nominal width | 7 mm |
| Volume | 1.227 cm ³ |
| Mounting position | Any |
| Structural design | Vacuum connection at top |
| Classification of suction cup holder | Size 5 |
| Operating medium | Atmospheric air based on ISO 8573-1:2010 [7:::-] |
| Corrosion resistance class (CRC) | 1 - Low corrosion stress |
| LABS (PWIS) conformity | VDMA24364-A1-L |
| Ambient temperature | -10 °C...60 °C |
| Product weight | 24 g |
| Type of mounting | With external thread Via vacuum connection |
| Suction cup mounting | M10 |
| Vacuum connection | G1/4 |
| Note on materials | RoHS-compliant |
| Seals material | Wrought aluminum alloy NBR POM Steel |
| Retaining bracket material | Tempered steel |