

Vacuum suction cup ESS-6-SN

Part number: 189274

FESTO



Data sheet

Feature	Value
Min. workpiece radius	15 mm
Nominal width	2 mm
Suction cup diameter	6 mm
Suction cup volume	0.015 cm ³
Ejector pulse suitability	4 bar
Connection position	Top
Mounting position	Any
Classification of suction cup holder	Size 2
Suction cup shape	Round, flat
Operating pressure	-95 kPa...0 kPa -0.95 bar...0 bar -13.775 psi...0 psi
Nominal operating pressure	-70 kPa -0.7 bar -10.15 psi
Operating medium	Atmospheric air based on ISO 8573-1:2010 [7:::]
Corrosion resistance class (CRC)	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-A1-L
For use in the food industry	See supplementary material information
Ambient temperature	-10 °C...70 °C
Holding force at nominal operating pressure	1.1 N
Lateral force at nominal operating pressure	3.5 N
Product weight	0.2 g
Type of mounting	Via vacuum connection
Vacuum connection	Inside diameter 4 mm
Color	Black
Shore hardness	50 +/- 5
Material of screwed plug	Brass, nickel-plated
Note on materials	RoHS-compliant
Suction cup material	NBR