

Vacuum suction cup

ESS-15-SU

Part number: 189290

FESTO



Data sheet

Feature	Value
Min. workpiece radius	35 mm
Nominal width	2 mm
Suction cup diameter	15 mm
Suction cup volume	0.208 cm ³
Connection position	Top
Mounting position	Any
Classification of suction cup holder	Size 3
Suction cup shape	Round, flat
Operating pressure	-95 kPa...0 kPa -0.95 bar...0 bar -13.775 psi...0 psi
Nominal operating pressure	-70 kPa -0.7 bar -10.15 psi
Operating medium	Atmospheric air based on ISO 8573-1:2010 [7:::-]
Corrosion resistance class (CRC)	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364 zone III
For use in the food industry	See supplementary material information
Ambient temperature	-20 °C...60 °C
Holding force at nominal operating pressure	8,5 N
Lateral force at nominal operating pressure	9 N
Product weight	1.9 g
Type of mounting	Via vacuum connection
Vacuum connection	M4
Color	Blue
Shore hardness	60 +/- 5
Material of screwed plug	Brass, nickel-plated
Note on materials	RoHS-compliant
Suction cup material	PUR