


Vacuum suction cup

ESS-40-SS

Part number: 189306

FESTO



Data sheet

| Feature | Value |
|---------------------------------------------|------------------------------------------------------------------------------------------------------|
| Min. workpiece radius | 230 mm |
| Nominal width | 3 mm |
| Suction cup diameter | 40 mm |
| Suction cup volume | 1.566 cm ³ |
| Connection position | Top |
| Mounting position | Any |
| Classification of suction cup holder | Size 4 |
| Suction cup shape | Round, flat |
| Operating pressure | -95 kPa...0 kPa -0.95 bar...0 bar -13.775 psi...0 psi |
| Nominal operating pressure | -70 kPa -0.7 bar -10.15 psi |
| Operating medium | Atmospheric air based on ISO 8573-1:2010 [7:::-] |
| Corrosion resistance class (CRC) | 1 - Low corrosion stress |
| LABS (PWIS) conformity | VDMA24364 zone III |
| For use in the food industry | See supplementary material information |
| Ambient temperature | -30 °C...180 °C |
| Holding force at nominal operating pressure | 69.6 N |
| Lateral force at nominal operating pressure | 25 N |
| Product weight | 16.3 g |
| Type of mounting | Via vacuum connection |
| Vacuum connection | M6 |
| Color | Transparent |
| Shore hardness | 50 +/- 5 |
| Material of screwed plug | Wrought aluminum alloy, nickel-plated Brass, nickel-plated Steel, galvanized and chrome-plated |
| Note on materials | RoHS-compliant |
| Suction cup material | VMQ (silicone) |