


Vacuum suction cup

ESS-200-SN

Part number: 189330

FESTO



Data sheet

Feature	Value
Min. workpiece radius	680 mm
Nominal width	10 mm
Suction cup diameter	200 mm
Suction cup volume	245.454 cm ³
Connection position	Top
Mounting position	Any
Classification of suction cup holder	Size 6
Suction cup shape	Round, flat
Operating pressure	-95 kPa...0 kPa -0.95 bar...0 bar -13.775 psi...0 psi
Nominal operating pressure	-70 kPa -0.7 bar -10.15 psi
Operating medium	Atmospheric air based on ISO 8573-1:2010 [7:-:-]
Corrosion resistance class (CRC)	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-A1-L
For use in the food industry	See supplementary material information
Ambient temperature	-10 °C...70 °C
Holding force at nominal operating pressure	1610 N
Lateral force at nominal operating pressure	850 N
Product weight	1198 g
Type of mounting	Via vacuum connection
Vacuum connection	M20x2
Color	Black
Shore hardness	50 +/- 5
Material of screwed plug	NBR Steel, nickel-plated Steel, galvanized and chrome-plated
Note on materials	RoHS-compliant
Suction cup material	NBR