

# Blanking plug QSC-5/8H-U

Part number: 190640

FESTO



## Data sheet

| Feature                                         | Value                                                             |
|-------------------------------------------------|-------------------------------------------------------------------|
| Size                                            | Standard                                                          |
| Mounting position                               | Any                                                               |
| Design                                          | Blanking plug                                                     |
| Pack size                                       | 1                                                                 |
| Structural design                               | Push-pull principle                                               |
| Operating pressure for entire temperature range | -0.095 MPa...1 MPa<br>-0.95 bar...10 bar<br>-13.775 psi...145 psi |
| Maritime classification                         | See certificate                                                   |
| Operating medium                                | Compressed air as per ISO 8573-1:2010 [7:::]                      |
| Information on operating and pilot media        | Operation with oil lubrication possible                           |
| Corrosion resistance class (CRC)                | 1 - Low corrosion stress                                          |
| LABS (PWIS) conformity                          | VDMA24364-B1/B2-L                                                 |
| Ambient temperature                             | -10 °C...60 °C                                                    |
| Product weight                                  | 4 g                                                               |
| Pneumatic connection 1                          | Push-in sleeve Ø 5/8"                                             |
| Ambient temperature Fahrenheit                  | 14 °F...140 °F                                                    |
| Releasing ring color                            | Gray                                                              |
| Note on materials                               | RoHS-compliant                                                    |
| Housing material                                | PBT                                                               |