

Non return valve
H-QS-3/8-U
Part number: 190845

FESTO



Data sheet

Feature	Value
Valve function	Non-return function
Pneumatic connection 1	QS-3/8
Pneumatic connection 2	QS-3/8
Type of mounting	Line installation
Standard nominal flow rate	1550 l/min
Operating pressure	-1 bar...10 bar
Ambient temperature	0 °C...60 °C
Housing material	Aluminum
Operating medium	Compressed air as per ISO 8573-1:2010 [7:::]
Min. differential pressure, opening	0.1 bar
Min. differential pressure, closing	0.2 bar
Information on operating and pilot media	Operation with oil lubrication possible (required for further use)
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Product weight	62 g
Note on materials	RoHS-compliant