

Non return valve
HA-1/8-QSM-3/16-U
Part number: 190849

FESTO



Data sheet

| Feature | Value |
|--|--|
| Valve function | Non-return function |
| Pneumatic connection 1 | 1/8 NPT |
| Pneumatic connection 2 | QS-3/16 |
| Type of mounting | Screw-in |
| Standard nominal flow rate | 238 l/min |
| Operating pressure | -1 bar...10 bar |
| Ambient temperature | 0 °C...60 °C |
| Housing material | Brass |
| Operating medium | Compressed air as per ISO 8573-1:2010 [7:::] |
| Min. differential pressure, opening | 0.1 bar |
| Min. differential pressure, closing | 0.2 bar |
| Information on operating and pilot media | Operation with oil lubrication possible (required for further use) |
| LABS (PWIS) conformity | VDMA24364-B2-L |
| Product weight | 13 g |
| Note on materials | RoHS-compliant |