

**Non return valve**  
**HA-1/4-QSM-3/16-U**  
Part number: 190852

**FESTO**



**Data sheet**

| Feature                                  | Value  |
|--|--|
| Valve function                           | Non-return function  |
| Pneumatic connection 1                   | 1/4 NPT  |
| Pneumatic connection 2                   | QS-3/16  |
| Type of mounting                         | Screw-in   |
| Standard nominal flow rate               | 238 l/min  |
| Operating pressure                       | -1 bar...10 bar  |
| Ambient temperature                      | 0 °C...60 °C   |
| Housing material                         | Brass  |
| Operating medium                         | Compressed air as per ISO 8573-1:2010 [7:::]                       |
| Min. differential pressure, opening      | 0.1 bar  |
| Min. differential pressure, closing      | 0.2 bar  |
| Information on operating and pilot media | Operation with oil lubrication possible (required for further use) |
| LABS (PWIS) conformity                   | VDMA24364-B2-L   |
| Product weight                           | 24 g   |
| Note on materials                        | RoHS-compliant   |