

Non return valve
HB-10-32-UNF-QSM-5/32-U
Part number: 190857

FESTO



Data sheet

Feature	Value
Valve function	Non-return function
Pneumatic connection 1	QS-5/32
Pneumatic connection 2	10-32 UNF-2A
Type of mounting	Screw-in
Standard nominal flow rate	145 l/min
Operating pressure	-1 bar...10 bar
Ambient temperature	0 °C...60 °C
Housing material	Brass
Operating medium	Compressed air as per ISO 8573-1:2010 [7:::]
Min. differential pressure, opening	0.1 bar
Min. differential pressure, closing	0.2 bar
Information on operating and pilot media	Operation with oil lubrication possible (required for further use)
LABS (PWIS) conformity	VDMA24364-B2-L
Product weight	7.2 g
Note on materials	RoHS-compliant