

Non return valve
HB-1/8-QSM-3/16-U
Part number: 190859

FESTO



Data sheet

Feature	Value
Valve function	Non-return function
Pneumatic connection 1	QS-3/16
Pneumatic connection 2	1/8 NPT
Type of mounting	Screw-in
Standard nominal flow rate	216 l/min
Operating pressure	-1 bar...10 bar
Ambient temperature	0 °C...60 °C
Housing material	Brass
Operating medium	Compressed air as per ISO 8573-1:2010 [7:::]
Min. differential pressure, opening	0.1 bar
Min. differential pressure, closing	0.2 bar
Information on operating and pilot media	Operation with oil lubrication possible (required for further use)
LABS (PWIS) conformity	VDMA24364-B2-L
Product weight	13 g
Note on materials	RoHS-compliant