


Vacuum filter ESF-4B

Part number: 191204

FESTO



Data sheet

Feature	Value
Mounting position	Any
Grade of filtration	10 µm
Operating pressure	-0.95 bar...4 bar
Flow rate at negative pressure = -0.75 bar	270 l/min
Operating medium	Atmospheric air based on ISO 8573-1:2010 [7:::-]
Corrosion resistance class (CRC)	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-A1-L
Ambient temperature	0 °C...60 °C
Product weight	19 g
Type of mounting	With external thread Via vacuum connection
Pneumatic connection	M6
Vacuum connection	M6
Note on materials	RoHS-compliant
Seals material	NBR
Compressed air filter material	PVF
Housing material	Aluminum Brass, nickel-plated