

Illuminating seal MC-LD-230AC

Part number: 19146

FESTO



Data sheet

Feature	Value
Switching position indication	LED
Type of mounting	On air solenoid valve with M3 central screw
Product weight	1.6 g
Electrical connection	Form A as per DIN EN 175301-803 Rectangular design MSC
Nominal operating voltage AC	230 V
Surge resistance	4 kV
Protective earth connection	Available
Nominal power luminous seal	0.33 W
Permissible voltage fluctuations	+/- 10 %
Degree of protection	IP65
Ambient temperature	-25 °C...85 °C
CE marking (see declaration of conformity)	As per EU low voltage directive
UKCA marking (see declaration of conformity)	To UK instructions for electrical equipment
LABS (PWIS) conformity	VDMA24364-B2-L
Contamination level	3
Housing material	TPE-U(PU)
Color	Transparent