

Plug socket MSSD-F-S-M16

Part number: 192746



Data sheet

Feature	Value
Contact durability	10
Type of mounting	On air solenoid valve with M3 central screw
Mounting position	Any
Product weight	35 g
Electrical connection	3-pin Socket Form B
Cable diameter	5.5 mm...8 mm
Nominal conductor cross section	0.5 mm ² ...1 mm ²
Degree of protection	IP67 as per IEC 60529
Ambient temperature	-25 °C...90 °C
LABS (PWIS) conformity	VDMA24364-B2-L
Housing material	PA
Housing colour	Black