

Stop element YSRWJ-7-10-A

Part number: 192967

FESTO



Data sheet

Feature	Value
Size	7
Stroke	10 mm
Cushioning	Self-adjusting Soft characteristic curve
Mounting position	Any
Precision adjustment	0.03 mm
Position sensing	For proximity sensor
Max. impact velocity	3 m/s
Reset time at room temperature	0.2 s
Reset time at min. ambient temperature	1 s
Mode of operation	Pushing Single-acting
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Ambient temperature	0 °C...60 °C
Cushioning length	10 mm
Max. stop force	300 N
Max. energy absorption per stroke	2 J
Max. energy absorption per hour	15000 J
Max. residual energy	0.01 J
Resetting force	1.7 N
Product weight	75 g
Type of mounting	With lock nut
Seals material	NBR
Housing material	Brass Nickel-plated
Piston rod material	High-alloy steel