

Plastic pipe
PQ-PA-28X2,5X3000
Part number: 194594



Data sheet

Feature	Value
Outside diameter	28 mm
Inside diameter	23 mm
Temperature-dependent operating pressure	-0.95 bar...10 bar
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Temperature of medium	-25 °C...75 °C
Ambient temperature	-25 °C...75 °C
Product weight by length	0.204 kg/m
Color	Black
Material of pneumatic tubing	PA