


# Precision pressure regulator

## LRPS-1/4-2,5

Part number: 194691

FESTO



## Data sheet

Feature	Value
Actuator lock	Rotary knob with integrated lock
Mounting position	Any
Structural design	Pilot-controlled precision diaphragm regulator
Controller function	Outlet pressure constant With secondary exhausting
Pressure gauge	G1/8 prepared
Operating pressure	0.1 MPa...1.2 MPa 1 bar...12 bar
Pressure regulation range	0.05 bar...2.5 bar
Inlet pressure 1	1 bar...12 bar
Max. pressure hysteresis	0.02 bar
Standard nominal flow rate	1800 l/min
Operating medium	Compressed air as per ISO 8573-1:2010 [7:4:4] Inert gas
Information on operating and pilot media	Operation with oil lubrication not possible
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Temperature of medium	-10 °C...60 °C
Ambient temperature	-10 °C...60 °C
Product weight	410 g
Type of mounting	Front panel mounting Line installation With accessories
Pneumatic connection 1	G1/4
Pneumatic connection 2	G3/4
Note on materials	RoHS-compliant
Seals material	NBR
Housing material	Aluminum