

# Rod eye CRSGS-M10X1,25

Part number: 195582

FESTO



## Data sheet

Feature	Value
Size	M10x1.25
Corrosion resistance class (CRC)	3 - High corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Suitability for the production of Li-ion batteries	Metals with more than 5% by mass of copper, zinc or nickel by mass are excluded from use. Exceptions are nickel in steel, chemically nickel-plated surfaces, printed circuit boards, cables, electrical plug connectors and coils
Ambient temperature	-40 °C...150 °C
Max. load capacity	0.9 kN
Product weight	87 g
Note on materials	RoHS-compliant
Material of outer ring	High-alloy steel
Housing material	High-alloy steel
Inner raceway material	High-alloy steel
Nut material	High-alloy steel