

Cable socket
ASI-SD-FK180
Part number: 196089



Data sheet

| Feature | Value |
|------------------------------------------------------|---------------------------|
| Type of mounting | With through-hole |
| Mounting position | Any |
| Product weight | 6.2 g |
| Electrical connection | 2-pin Socket, straight |
| DC operating voltage range | 75 V |
| Operating voltage range AC | 60 V |
| Current rating | 3 A |
| Connection cross section | 1.5 mm ² |
| Degree of protection | IP65 |
| Ambient temperature with flexible cable installation | -5 °C...50 °C |
| Storage temperature | -30 °C...85 °C |
| LABS (PWIS) conformity | VDMA24364-B2-L |
| Note on materials | RoHS-compliant |
| Housing material | PA |
| Material of pin contacts | Bronze |