

Mounting plate VN-T6-BP-NRH

Part number: 196956

FESTO



Data sheet

Feature	Value
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Ambient temperature	0 °C...60 °C
Max. tightening torque	0.8 Nm
Product weight	12.4 g
Type of mounting	With through-hole With H-rail
Note on materials	RoHS-compliant
Plate material	PA-reinforced
Gate valve material	POM