

Soldering base PCBC-A-10

Part number: 197 261

FESTO



Data sheet

Feature	Value
Type of mounting	With soldering base
Mounting position	Any
Product weight	5 g
Pack size	10
Electrical connection	2-pin
Degree of protection	IP40
Ambient temperature	-40 °C...115 °C
LABS (PWIS) conformity	VDMA24364-B2-L
Housing material	PA