

Pneumatic muffler

UO-1/4

Part number: 197584

FESTO



Data sheet

Feature	Value
Mounting position	Any
Structural design	Pneumatic muffler, open
Operating pressure	0 MPa...0.8 MPa 0 bar...8 bar
Operating medium	Compressed air as per ISO 8573-1:2010 [7:4:4]
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Ambient temperature	-10 °C...60 °C
Product weight	8 g
Pneumatic connection	G1/4
Cushioning insert material	PE
Material of screwed plug	PE
Note on materials	RoHS-compliant