

Spiral plastic tubing PUN-8X1,25-S-1-SW

Part number: 197608

FESTO



Data sheet

Feature	Value
Working length	1 m
Outside diameter	8 mm
Block length	0.304 m
Inside diameter	5.7 mm
Winding diameter	60 mm
Number of windings	12
Temperature-dependent operating pressure	-0.095 MPa...1 MPa -0.95 bar...10 bar -13.775 psi...145 psi
Certification	German Technical Control Board (TÜV)
Certificate issuing authority	B 013277 0506 00
Operating medium	Compressed air as per ISO 8573-1:2010 [7::-]
LABS (PWIS) conformity	VDMA24364-B2-L
Ambient temperature	-35 °C...60 °C
Product weight	65 g
Pneumatic connection	For plug connection outside diameter 8 mm For barbed fitting, inside diameter 6 mm, with union nut For barbed fitting, inside diameter 6 mm
Color	Black
Shore hardness	D 52 +/-3
Material of pneumatic tubing	TPE-U(PU)