


Axial kit
EAMM-A-D19-40P
Part number: 1981953



Data sheet

Feature	Value
Nominal length	45.7 mm
Mounting position	Any
Max. rotational speed	10000 rpm
LABS (PWIS) conformity	VDMA24364 zone III
Storage temperature	-25 °C...60 °C
Relative air humidity	0 - 95 %
Degree of protection	IP40
Ambient temperature	-10 °C...60 °C
Mass moment of inertia	0.28 kgmm ²
Transferable torque	1.1 Nm
Product weight	110 g
Interface code, actuator	D19
Interface code, motor in	40P
Note on materials	RoHS-compliant