


Axial kit
EAMM-A-P5-28B-40P
Part number: 1983122



Data sheet

Feature	Value
Nominal length	12.5 mm
Mounting position	Any
Max. rotational speed	10000 rpm
LABS (PWIS) conformity	VDMA24364-B2-L
Storage temperature	-25 °C...60 °C
Relative air humidity	0 - 95 %
Degree of protection	IP40
Ambient temperature	-10 °C...60 °C
Mass moment of inertia	0.28 kgmm ²
Transferable torque	1.1 Nm
Product weight	50 g
Interface code, actuator	P5-28B
Interface code, motor in	40P
Interface code, coupling housing	28B
Note on materials	RoHS-compliant