

Axial kit
EAMM-A-P10-38A-60P
Part number: 2036017



Data sheet

Feature	Value
Nominal length	21 mm
Mounting position	Any
Max. rotational speed	8000 rpm
LABS (PWIS) conformity	VDMA24364-B2-L
Storage temperature	-25 °C...60 °C
Relative air humidity	0 - 95 %
Degree of protection	IP40
Ambient temperature	-10 °C...60 °C
Mass moment of inertia	5.87 kgmm ²
Transferable torque	12.5 Nm
Product weight	210 g
Interface code, actuator	P10-38A
Interface code, motor in	60P
Interface code, coupling housing	38A
Note on materials	RoHS-compliant