

Rotary distributor GF-1/4

Part number: 2094

FESTO



Data sheet

Feature	Value
Nominal width	11.5 mm
Mounting position	Any
Operating pressure for entire temperature range	-0.095 MPa...1 MPa -0.95 bar...10 bar -13.775 psi...145 psi
Standard flow rate 1-2.1 (6->0)	2932 l/min
Standard flow rate 1-2.X open (6->0)	2977 l/min
Standard nominal flow rate 1.1-2.1	1792 l/min
Max. rotational speed	300 rpm
Operating medium	Compressed air as per ISO 8573-1:2010 [7:::]
Information on operating and pilot media	Operation with oil lubrication possible (required for further use)
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Temperature of medium	-10 °C...60 °C
Ambient temperature	-10 °C...60 °C
Product weight	250 g
Pneumatic connection 1	External thread G1/4
Pneumatic connection 2	Internal thread G1/4
Note on materials	RoHS-compliant
Housing material	Wrought aluminum alloy
Shaft material	High-alloy steel