

Union nut
MCK-PK-3-KU
Part number: 211289

FESTO



Data sheet

Feature	Value
Size	Internal thread M6x0.75
Operating pressure for entire temperature range	0 MPa...1 MPa 0 bar...10 bar 0 psi...145 psi
LABS (PWIS) conformity	VDMA24364-B2-L
Ambient temperature	-10 °C...60 °C
Pneumatic connection 1	for pneumatic tubing outside diameter 4 mm For barbed fitting, inside diameter 3 mm, with union nut
Material of union nut	POM
Note on materials	RoHS-compliant