

Quick coupling plug KS4-1/4-A

Part number: 2154

FESTO



Data sheet

Feature	Value
Nominal width	7.85 mm
Operating pressure for entire temperature range	-0.095 MPa...1.2 MPa -0.95 bar...12 bar -13.775 psi...174 psi
Normal nominal flow rate (normalized to DIN 1343)	756 l/min...1323 l/min
Nominal flow rate standardized according to ISO 8778	819.5 l/min...1434.1 l/min
Operating medium	Compressed air as per ISO 8573-1:2010 [7:::]
Information on operating and pilot media	Operation with oil lubrication possible
Corrosion resistance class (CRC)	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Ambient temperature	-10 °C...60 °C
Nominal tightening torque	9.5 Nm
Tolerance for nominal tightening torque	± 15%
Product weight	21 g
Pneumatic connection 1	External thread G1/4
Note on materials	RoHS-compliant
Material of threaded seal	PA66-GF30/TPE-U
Information on materials	Brass, nickel-plated