


**Axial kit**  
**EAMM-A-D60-100A-S1**  
Part number: 2256700



**Data sheet**

| Feature                  | Value                  |
|--------------------------|------------------------|
| Nominal length           | 79.2 mm                |
| Mounting position        | Any                    |
| Max. rotational speed    | 6000 rpm               |
| LABS (PWIS) conformity   | VDMA24364 zone III     |
| Storage temperature      | -25 °C...60 °C         |
| Relative air humidity    | 0 - 95 %               |
| Degree of protection     | IP65                   |
| Ambient temperature      | -10 °C...60 °C         |
| Mass moment of inertia   | 34.8 kgmm <sup>2</sup> |
| Transferable torque      | 17 Nm                  |
| Product weight           | 1170 g                 |
| Interface code, actuator | D60                    |
| Interface code, motor in | 100A                   |
| Note on materials        | RoHS-compliant         |