


Flanged pressure gauge FMA-63-0,25-C

Part number: 225783

FESTO



Data sheet

Feature	Value
Display range	0 bar...0.25 bar 0 psi...3.6 psi
Conforms to standard	EN 837-3
Pressure gauge nominal size	63
Explosion prevention and protection	Observe the information on the certificate Zone 1 (ATEX) Zone 2 (ATEX) Zone 21 (ATEX) Zone 22 (ATEX)
Type of mounting	Front panel mounting
Operating medium	Liquid media Gaseous media
Information on operating and pilot media	No acetylene No oxygen
Operating pressure	0 bar...0.25 bar
Intermittent load factor	0.9
Continuous load factor	0.75
Measurement accuracy class	1.6
Degree of protection	IP43
Temperature of medium	-20 °C...80 °C
Ambient temperature	-20 °C...60 °C
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Connection position	Centered on rear side
Pneumatic connection	G1/4
Material of screwed plug	Brass
Housing material	Steel
Inspection window material	PMMA
Fastening ring material	Steel
Material of screws	Steel
Product weight	120 g